

High Temperature Thermostat using the unistat principal with Plug & Play technology. Minimized volume, shortest possible heating times, hydraulically closed: No oil vapour. Housing made of stainless steel. With adjustable overtemperature protection according to DIN 12876. Length of cable between machine and controller approx. 5m. Speed controlled pump (soft start), pump pressure control.

## Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

## Further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

4-year warranty - registration required.

## Technical data according to DIN 12876

|                                 |                                       |
|---------------------------------|---------------------------------------|
| Operating temperature range     | 50...400 °C                           |
| Resolution of display           | 0,01 K                                |
| Temperature stability at 70°C   | 0,05 K                                |
| temperature set point / display | 5,7" colour Touchscreen               |
| Absolute accuracy               | 2-point-calibration                   |
| Internal temperature sensor     | Pt100                                 |
| External sensor                 | Pt100                                 |
| Interface digital               | Ethernet, USB (Host u. Device), RS232 |
| digital input                   | ECS ONE                               |
| digital output                  | POKO ONE                              |
| Alarm message                   | optic, acoustic, relay                |
| Safety classification           | III / FL                              |
| Heating power at 240V           | 3 kW                                  |
| Heating power at 230V           | 3 kW                                  |
| Heating power at 220V           | 2,7 kW                                |
| Heating power at 208V           | 2,4 kW                                |
| Heating power at 200V           | 2,2 kW                                |
| Circulation pump:               |                                       |
| max. delivery                   | 31 l/min                              |
| max. delivery pressure          | 0,9 bar                               |
| Pump connection flow            | M24x1,5                               |
| Pump connection return          | M24x1,5                               |
| Cooling water connection        | G1/2 male                             |
| min. filling capacity           | 2,3 l                                 |
| Volume of expansion             | 5 l                                   |
| Overall dimensions WxDxH        | 288x379x890 mm                        |
| Pressure equipment category     | Art. 4.3 PED                          |
| Degree of Protection            | IP20                                  |
| Net weight                      | 55 kg                                 |
| Power supply requirement        | 200-240V 1~/2~ 50/60Hz                |
| max. current                    | 14 A                                  |
| Fuse                            | 16 A                                  |
| min. ambient temperature        | 5 °C                                  |
| max. ambient temperature        | 40 °C                                 |



**Order-No.: 1028.0007.01**

**from Serial-No.: 408106**

**1.1/20**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

## Technical data according to DIN 12876

---

### Included Accessories:

E-grade "Professional" #9496, mini-USB cable #54949, Cover level indicator, connection cable (order no.: 13482),

### Optional accessories:

software & interfaces, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and + 3% frequency -> not allowed !

-10% voltage and -3% frequency -> allowed.

### Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Attention: leakage current externe Temperierung

### Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)