

**Technical data**

Operating temperature range	-90...230 °C
Operating temperature	20 °C
Material	stainless steel 1.4404, 1.4571
Sealing material	Special material, PTFE
Nennweite	20 mm
Outside diameter	54 mm
Length	113 mm
Net weight	0,915 kg
Connection	M30x1,5 male
Location	Temperature control unit, application
Max. pressure at 20°C	25 bar
Leakage rate *	<0,4 ml per decoupling cycle
Cv value *	14

**Order-No.: 10407****1.0/18**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

## Included Accessories:

Winkelanschluss 90° #10450,

## Optional accessories:

Verschlussnippel #10406, Druckentlastungseinrichtung #10417, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Bore shape Y (60°) to DIN 3863, piping/temperature hoses: Connectors to DIN 3863

\* Measured with water (20° C) at an ambient temperature of 20° C.

## Note:

When using ethanol as thermofluid: min. working temperature limit -60° C.