

Closed magnetic-coupled circulation pump with integrated overload protection. Housing of stainless steel with 2 handles. Operation either manual (on/off) or external via 3-line-connector. Control cable (option) for the potential free contact of Unistat Tango and the big power Unistats, all Compatible Control Thermostats and Unichillers.

## Technical data according to DIN 12876

Operating temperature range	-120...350 °C
Circulation pump	MK pump
max. delivery of pressure pump	120 l/min
max. delivery pressure	4 bar
Delivery at 1,0 bar	85 l/min
Delivery at 2,0 bar	54 l/min
Delivery at 3,0 bar	27 l/min
Pump connection	M38x1,5 male
Overall dimensions WxDxH **	275x420x295 mm
Net weight	27 kg
Geräuschpegel	71 dB(A)
Power supply (3 Phase)	380-480V 3~ 50/60Hz
max. current (3 Phase)	2,5 A
Fuse (3 phase)	3x4A
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C



Order-No.: 1087.0001.00

from Serial-No.:	417303	1.0/21
------------------	--------	--------

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:  
bridge plug #6478

Optional accessories:  
control cable #6221, temperature control / - connection hoses, adapters, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)