

Refrigerated Heating Circulator Bath with air-cooled cooling machine. Powerful, variable speed, pressure and suction pump, evaporator (cooler) and housing of stainless steel, CFC and H-CFC free. With adjustable overtemperature protection according to DIN 12876.

#### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

#### Technical data according to DIN 12876

Operating temperature range	-40...200 °C
Temperature stability at -10°C	0,02 K
temperature set point / display	5,7" colour Touchscreen
Internal temperature sensor	Pt100
Sensor external connection	Pt100
Interface digital	Ethernet, USB (Host u. Device), RS232
Safety classification	III / FL
Heating power	1,5 kW
Cooling power	
at 100°C	0,42 kW
at 20°C	0,42 kW
at 0°C	0,38 kW
at -10°C	0,33 kW
at -20°C	0,25 kW
at -30°C	0,14 kW
at -40°C	0,05 kW
Refrigeration machine	air-cooled, natural refrigerant
Refrigerant (ASHRAE, GHS)	R-290 (A3, H220)
Global Warming Potential (GWP)	0,02
Refrigerant quantity	0,099 kg
Gas warning sensor	without
Pressure pump	yes
max. delivery	22 l/min
max. delivery pressure	0,7 bar
Suction pump	yes
max. delivery (suction)	16 l/min
max. delivery pressure (suction)	0,4 bar
Pump connection	M16x1 male
max. permissible kin. viscosity	50 mm <sup>2</sup> /s
Bath volume	3,5 l
min. filling capacity	3 l
Bath capacity with displacement rack	1,7 l
Width bath opening WxD / bath depth	170 x 85 / 135 mm
Overall dimensions WxDxH **	255x450x476 mm



**Order-No.: 2015.0012.01**

## Technical data according to DIN 12876

---

Net weight	37 kg
Power supply requirement	110-120V 1~ 60Hz
max. current	14 A
Fuse	16 A
Pressure equipment category	Art. 4.3 PED
Degree of Protection	IP20
max. ambient temperature	40 °C
min. ambient temperature	5 °C

---

**from Serial-No.:** **401064** **1.4/20**

---

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini USB cable #54949, blank plug , hose connector NW12 , sleeve nuts thread , bath cover .

Optional accessories:

drain valve, displacement insert to reduce bath volume, calibration insert, Com.G@te, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C. If the ambient temperature rises, the cooling capacity may drop.

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)