

Refrigerated Heating Circulator Bath with air-cooled cooling machine. Powerful, variable speed, pressure and suction pump, evaporator (cooler) and housing of stainless steel, CFC and H-CFC free. With adjustable overtemperature protection according to DIN 12876.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

Technical data according to DIN 12876

| | |
|--------------------------------------|---------------------------------------|
| Operating temperature range | -55...200 °C |
| Temperature stability at -10°C | 0,02 K |
| temperature set point / display | 5,7" colour Touchscreen |
| Internal temperature sensor | Pt100 |
| Sensor external connection | Pt100 |
| Interface digital | Ethernet, USB (Host u. Device), RS232 |
| Safety classification | III / FL |
| Heating power | 1,5 kW |
| Cooling power | |
| at 100°C | 3,3 kW |
| at 20°C | 3,3 kW |
| at 0°C | 3,3 kW |
| at -20°C | 1,6 kW |
| at -40°C | 0,6 kW |
| Refrigeration machine | air-cooled, CFC- and HCFC-free |
| Refrigerant (ASHRAE, GHS) | R-452A (A1, H280) |
| Global Warming Potential (GWP) | 2141 |
| Refrigerant quantity | 1,5 kg |
| Pressure pump | yes |
| max. delivery | 25 l/min |
| max. delivery pressure | 0,7 bar |
| Suction pump | yes |
| max. delivery (suction) | 18,5 l/min |
| max. delivery pressure (suction) | 0,4 bar |
| Pump connection | M16x1 male |
| max. permissible kin. viscosity | 50 mm²/s |
| Bath volume | 26 l |
| min. filling capacity | 19 l |
| Bath capacity with displacement rack | 15 l |
| Width bath opening WxD / bath depth | 260 x 260 / 200 mm |
| Height of bath opening | 937 mm |
| Overall dimensions WxDxH ** | 605x706x1136 mm |
| Net weight | 142 kg |
| Power supply requirement (3 phase) | 208V 3~ 60Hz |



Order-No.: 2021.0003.01

Technical data according to DIN 12876

| | |
|-----------------------------|--------------|
| max. current (3 Phase) | 13,5 A |
| Fuse (3 phase) | 3x16A |
| Pressure equipment category | Art. 4.3 PED |
| Degree of Protection | IP20 |
| max. ambient temperature | 40 °C |
| min. ambient temperature | 5 °C |

| | | |
|-------------------------|---------------|---------------|
| from Serial-No.: | 536192 | 1.4/23 |
|-------------------------|---------------|---------------|

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini USB cable #54949, blank plug, hose connector NW12, sleeve nuts thread, bath cover.

Optional accessories:

drain valve, displacement insert to reduce bath volume, calibration insert, Com.G@te, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com