

Chiller with water-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications. With adjustable overtemperature protection according to DIN 12876.

## Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

The dimensions specified below are approximate and may be subject to change.

## Technical data according to DIN 12876

Operating temperature range	-20...100 °C	
temperature set point / display	5,7" colour Touchscreen	
Internal temperature sensor	Pt100	<b>Order-No.: 3057.0016.01</b>
Sensor external connection	Pt100	
Temperature stability at -10°C	0,2 K	
Interface digital	Ethernet, USB (Host u. Device), RS232	
Safety classification	III / FL	
Heating power	2 kW	
Cooling power		
at 15°C	25 kW	
at 0°C	18 kW	
at -10°C	11 kW	
at -20°C	6 kW	
Refrigeration machine	water-cooled, natural refrigerant	
Refrigerant (ASHRAE, GHS)	R-290 (A3, H220)	
Global Warming Potential (GWP)	0,02	
UN-number	UN 3358	
Circulation pump	D3	
max. delivery	210 l/min	
max. delivery pressure	4,7 bar	
Delivery at 1,1 bar	202 l/min	
Delivery at 1,5 bar	193 l/min	
Delivery at 2,0 bar	179 l/min	
Delivery at 2,5 bar	159 l/min	
Delivery at 3,0 bar	140 l/min	
Delivery at 3,5 bar	115 l/min	
Delivery at 4,0 bar	77 l/min	
Delivery at 4,5 bar	31 l/min	
Pump connection	G1 1/4 male	
Cooling water connection	G3/4 male	
min. cooling water differential pressure	1 bar	
max. cooling water pressure	6 bar	

## Technical data according to DIN 12876

min. filling capacity	15 l
Volume of expansion	22 l
Overall dimensions WxDxH **	760x840x1767 mm
Power supply (3 Phase)	400V 3~ 50Hz
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

from Serial-No.:

1.0/24

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

### Included Accessories:

mini-USB cable #54949, cover expansion vessel, Hose coupling for G1 1/4 male, hose coupling cooling water for G3/4 male

### Optional accessories:

Com.G@te, external sensor, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Note: Connection option for extract ventilation

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 1 bar differential pressure between cooling water inlet and - outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materials used in the cooling water circuit include: copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

### Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

### Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)