

Technical data

Operating temperature range	-100...350 °C
Material	stainless steel, 1.4404
Braiding	no
Nominal width (DN)	25 mm
Length	300 cm
Net weight	5,5 kg
Connection	M38x1,5
Outside diameter	63 mm
Max. pressure at 20°C	16 bar
maximaler Druck bei 350 °C	10 bar
Test pressure	1,25 bar
Min. bending radius	240 mm
Fire rating	UL94-HB

**Order-No.: 6658****1.1/25**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.