

The Unical 700 is a isolated calibration bath of stainless stell. The temperature level is controlled by a Unistat connected to it using hoses and is therewith limited. This results in good mixing characteristics and a homogeneous temperature distribution within the bath.

width with overflow vessel: 440mm

**Technical data**

Operating temperature range	-100...300 °C
Temperature stability at -10°C	0,002 K
Pump connection	M30x1,5 male
Bath opening diameter	118 mm
Bath depth	385 mm
Bath volume	7 l
Overall dimensions WxDxH **	300x300x566 mm
Net weight	23 kg



**Order-No.: 9623**

**1.0/18**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: bath cover PTFE #6365, bath cover PE #6366, bath cover stainless steel #6367

\* standard equipment

Output data valid for: Room temperature 20° C

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)